






## Specifications and rated capacity in pounds.

Color Code	Stock Number	Approx. body diameter inches	Approx. body wt. / ft. pounds	 Vertical	 Choker	 Basket	 60°	 45°
Purple	FG 0600	0.60	0.30	2,600	2,100	5,200	4,500	3,700
Green	FG 0800	0.80	0.40	5,300	4,200	10,600	9,200	7,500
Yellow	FG 1000	1.00	0.50	8,400	6,700	16,800	14,500	11,900
Tan	FG 1200	1.20	0.60	10,600	8,500	21,200	18,400	15,000
Red	FG 1300	1.30	0.80	13,200	10,600	26,400	22,900	18,700
White	FG 1400	1.40	0.90	16,800	13,400	33,600	29,100	23,800
Blue	FG 1550	1.55	1.20	21,200	17,000	42,400	36,700	30,000
Orange	FG 1750	1.75	1.50	25,000	20,000	50,000	43,300	35,400
Orange	FG 1950	1.95	2.00	31,000	24,800	62,000	53,700	43,800
Orange	FG 2350	2.35	2.80	40,000	32,000	80,000	69,300	56,600
Orange	FG 3150	3.15	3.60	53,000	42,400	106,000	91,800	74,900
Orange	FG 3950	3.95	4.60	66,000	52,800	132,000	114,300	93,300
Orange	FG 4800	4.80	5.80	90,000	72,000	180,000	155,900	127,300

### Inspect your slings regularly.

Before each lift, visually inspect your Flexi-grip sling for any damage. Remove sling from service if you see:

- Missing or illegible identification tag.
- Melting, charring or weld spatter on any part of the sling.
- Holes, tears, cuts, embedded particles, abrasive wear or snags that expose the sling's core yarns.
- Broken or worn stitching in the cover that exposes the core yarns.
- Fittings that are damaged, stretched, cracked, pitted or distorted in any way.
- Knotting in the sling.
- Acid or alkali burns.
- Other visible damage that causes doubt as to the sling's strength.
- Loading a sling beyond its rated capacity.

### Match the color to your lifting needs.

The jackets of Flexi-grip slings are color-coded by rated capacity. Choose from eight different colors to fit the rated capacity you need for your lift (see chart). Each sling also features a durable identification tag to indicate its size, type and rated capacity for your convenience.

### Be careful.

- Do not expose Flexi-grip slings to strong alkalis at elevated temperatures, and never use at temperatures above 194° F (90° C) or below -40°F(-40°C).
  - Avoid sling contact with any kind of sharp surfaces.
  - Do not overload any sling beyond its rated capacity to prevent permanent stretch and weakening.
- Warning:** Failure to follow proper care, use and inspection criteria may result in personal injury. Do not exceed rated capacities.

### Flexi-grip options.

Flexi-grip slings are also available in three configurations:

- Endless-type slings that double the lifting legs in every application.
  - Multi-leg bridles.
  - Eye and eye slings formed by enclosing the body of an endless sling in a tubular jacket for extra protection and durability.
- Moveable wear pads made with durable polyester buffer or leather are also available to help protect against lifting hooks and corners of loads.